



### Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	230/460 V
Current	44/22 A	Speed	1730 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Frame	215TZ	Enclosure	Open Drip Proof
Thermal Protection	No	Ambient Temperature	40 °C
UL	Recognized	CSA	Y
CE	Y	Number of Speeds	1

### Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Counterclockwise
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Keyed	Overall Length	19.59 in
Frame Length	12.40 in	Shaft Diameter	1.375 in
Shaft Extension	3.76 in		
Connection Drawing	A-EE9048NB-CY	Outline Drawing	037779CY

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/12/2021