



Nameplate Specifications

Phase	3	Output HP	3.0 Hp
Voltage	460 V	Speed	1760 rpm
Service Factor	1.15	Frame	182T
Enclosure	Totally Enclosed Non Ventilated	Thermal Protection	No Protection
Efficiency	90.2 %	Ambient Temperature	40 °C
Frequency	60 Hz	Current	4.0 A
Duty	Continuous	Insulation Class	F

Technical Specifications

Poles	4	Rotation	Reversible
Mounting	Rigid Base	Drive End Bearing	Ball
Opp Drive End Bearing	Ball		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/05/2023