

PRODUCT INFORMATION PACKET



Model No: 533389-3

Catalog No: 533389-3

B-533389-3 POTENTIAL TRANSFORMER RESIN CAST (4200V : 120V -3PH) -FUSED

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E




Nameplate Specifications

Technical Specifications



This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/05/2025

4					3			2				1		
DASH	ITEM REV.	RATED FREQ.	THERMAL RATED VA @ 55° C		GROUP	CATALOG NUMBER FUSES	CATALOG NUMBER FUSES CLIPS ONLY	VOLTAGE RATING		RATIO	SUGGESTED FUSE RATING	VENDOR	REMARKS	APPROX. WEIGHT
			TOTAL	PER PHASE				PRIMARY	SECONDARY					
-1	0	60 HZ	450	225	1	3PT3-60-242FFF	3PT3-60-242CCC	2400	120	20:1	1.0E	ITI / GE MULTILIN		38 LB
-2	0	60 HZ	350	-	2	3PT3-60-332FFF	3PT3-60-332CCC	3300	120	30:1	1.0E	ITI / GE MULTILIN		38 LB
-3	0	60 HZ	450	225	2	3PT3-60-422FFF	3PT3-60-422CCC	4200	120	35:1	0.5E	ITI / GE MULTILIN		38 LB
-4	0	60 HZ	450	225	2	3PT3-60-482FFF	3PT3-60-482CCC	4800	120	40:1	0.5E	ITI / GE MULTILIN		38 LB


B





A



REMOVE COMPRESSION LUGS BEFORE ASSEMBLY (NOT USED)



NOTE:
** CSA CERTIFIED PT**

DRAWING REVISION F		REVISION BY TM		REV DATE/© DATE 07-06-2022		TOLERANCES (EXCEPT AS NOTED): DEC. INCH mm ANGLE .X ±0.1 [±3] ±7° 30" .XX ±0.02 [±0.5] .XXX ±0.005 [±0.13] .XXXX ±0.0005 [±0.013] REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.08/.38] X 45° CORNER FILLETS: R.02 [.5] MACHINED SURFACES: 200 INCH mm 5.1 mm DIMENSIONS IN [BRACKETS] ARE FOR REFERENCE ONLY				DRAWN BY CLJ		<div></div> <div>Regal Beloit America, Inc.</div>			
REQUEST NUMBER NMR-0215033		APPROVED BY CDP		DATE 07-06-2022						DATE 05-08-2013					
REQUEST NUMBER DESCRIPTION TOL. BLOCK WAS .01 <div>COPYRIGHT (PER REVISION DATE) REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.</div>										APPROVED BY JER		DESCRIPTION TRANSFORMER POTENTIAL TRANSFORMER -FUSED			
										DATE 05-08-2013					
										REFERENCE 527955		MATERIAL		PROCESS/FINISH	
										THIRD ANGLE PROJECTION 		SIZE B	DRAWING NUMBER 533389		SHEET 1 OF 1