

PRODUCT INFORMATION PACKET



Model No: 503444L-AV
Catalog No: 503444L-AV
B-503444L-AV BRKT MCH/312/LKD/.75 BAF (SOURCED w/SCREENS)


Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/05/2025



- DIMENSIONS MUST BE INSPECTED BEFORE PARTS SHIP FROM SUPPLIER

SCREEN	Q
554431	4

DRAWING REVISION	REVISION BY	DATE
C	AJW	04-02-2015
ECO	APPROVED BY	DATE
ECO-0074794	DJK	04-02-2015
ECO DESCRIPTION		
.961/.966 WAS .936/.941		
COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.		

TOLERANCES UNLESS OTHERWISE SPECIFIED:			
DEC.	INCH	mm	ANGLE
.X	±0.1	[±2.5]	±7° 30"
.XX	±0.02	[±0.51]	
.XXX	±0.005	[±0.127]	
.XXXX	±0.0005	[±0.0127]	
REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.076/.381] X 45°			
CORNER FILLETS: R.02 [.51]			
MACHINED SURFACES: 200 INCH mm 5.1			
mm SHOWN IN [BRACKETS]			

DRAWN BY	TJW
DATE	6/3/2011
APPROVED BY	LC
DATE	6/3/2011
REFERENCE	CSTG 503444
THIRD ANGLE PROJECTION	

Regal Beloit America, Inc.			
DESCRIPTION			
END FRAME-MACHINED			
360 FR.-312 BRG - VERT			
MATERIAL		PROCESS/FINISH	
		200 MAX U.S.O.	
SIZE	DRAWING NUMBER	SHEET	
B	503444L	1 OF 1	