

PRODUCT INFORMATION PACKET



Model No: S9225-21
Catalog No: S9225-21
THREAD FORMING SCREW (ROLLING)



















Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/05/2025

UNLESS OTHERWISE SPECIFIED ALL SCREWS TO BE PLATED PER E1817-1												S9225												
												HEAD TYPE			SCREW TYPE									
△56 S #10-24 .31 BB PHILLIPS						*81 T #10-32 .75 MM IND.HX WSH W/SERR.						AA		ROUND	D		THREAD CUTTING							
-55 S #10-24 .38 JJ SLOT HEX						*80 F 1/4-20 1.00 BB PAN OR BINDING						BB		PAN OR BINDING	T		THREAD CUTTING							
-54 F #6-32 .31 BB PHILLIPS						-79 T 5/16-18 1.25 MM IND.HX WSH W/SERR.						CC		TRUSS OR STOVE	F		THREAD CUTTING							
-53 T 3/8-16 1.00 HH HEX						-78 T 1/4-20 1.00 MM IND.HX WSH W/SERR.						DD		FLAT	S		TYPE SF							
-52 T #8-32 1.00 JJ SLOT HEX						-77 T #10-32 .75 MM IND.HX WSH W/SERR.												EE		OVAL		TYPE SW		
-51 T #8-32 .50 BB PHILLIPS						-76 D #10-24 1.00 HH HEX												FF		FILLISTER				TYPE TRI-LOBE THREAD ROLLING
-50 (06-24-1988)						-75 S 5/16-18 .62 MM IND.HX WSH W/SERR.												GG		INDENTED HEX				
-49 S #10-24 .50 JJ SLOT HEX						-74 S #10-32 .50 LL SLOT HEX W/SERR.												HH		INDENTED HEX WASHER				
-48 (07-07-1987)						-73 S #10-32 .38 LL SLOT HEX W/SERR.												JJ		SLOTTED HEX WASHER				
-47 S 5/16-18 1.25 HH HEX						-72 S 5/16-18 .50 HH HEX						KK		SLOTTED HEX	SCREWS TO MEET ANSI-B-18.64-1958 SPECIFICATIONS.									
-46 S #10-24 .50 HH HEX						-71 F #8-32 .38 JJ SLOT HEX						LL		SLOTTED HEX WASHER WITH SERR.	* STAINLESS 18-8 OR 410									
-45 S 1/4-20 .75 HH HEX						□70 S 1/4-20 .38 LL SLOT HEX W/SERR.						MM		INDENTED HEX WASHER WITH SERR.	△ TO BE IRRADATE GREEN COATED									
-42 CANCELLED PER CR-85680						-69 S #6-32 .75 BB PHILLIPS						BUY												
-40 S 5/16-18 1.75 JJ SLOT HEX						□68 T 1/4-20 .50 JJ HEX																		
-36 D #10-24 .75 BB PHILLIPS						-67 (03-22-1994)																		
-32 S 1/4-20 .62 BB PHILLIPS						□66 S 1/4-20 .75 HH HEX																		
-30 T #10-24 .50 AA PHILLIPS						□65 S 1/4-20 .50 JJ HEX																		
-28 S 3/8-16 .75 HH HEX						□64 S 5/16-18 .62 JJ SLOT HEX																		
-26 S 5/16-18 .62 JJ SLOT HEX						□63 D #10-24 .75 BB PHILLIPS																		
-22 S 5/16-18 .88 JJ HEX						-62 S #6-32 .38 BB PHILLIPS																		
-21 S #10-24 .50 BB SLOT						□61 S #10-24 .38 BB PHILLIPS																		
-17 S 1/4-20 1.00 JJ SLOT HEX						-60 T 3/8-16 1.25 HH HEX																		
-9 USE S-9225-30						-59 S 5/16-18 .38 HH HEX																		
-8 S 1/4-20 .50 JJ HEX						-58 T 3/8-16 .50 HH HEX																		
-4 S #10-24 .38 BB PHILLIPS						-57 S 5/16-18 1.00 HH HEX																		
PART NO.	TYPE	SIZE	LENGTH	HEAD TYPE	STYLE	PART NO.	TYPE	SIZE	LENGTH	HEAD TYPE	STYLE													