

Nameplate Specifications

Phase	3	Output HP	5 Hp
Output KW	3.7 kW	Voltage	230/460 V
Speed	1140 r/min	Service Factor	1
Frame	180	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Thermostat	Ambient Temperature	40 °C
Frequency	60 Hz	Current	16.0/8.0 A
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	L
UL	No	CSA	N
CE	N	IP Code	-
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Mounting	PARTIAL MOTOR	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	IEC	Assembly/Box Mounting	VERIFY
Connection Drawing	005010.19	Outline Drawing	OL131364

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:10/24/2025