

PRODUCT INFORMATION PACKET



Model No: 184TBFW17015
Catalog No: 184TBFW17015
4,3600,TEFC,184T,1/60/208


Nameplate Specifications

Phase	1	Output HP	4 Hp
Output KW	3.0 kW	Voltage	208 V
Speed	3535 r/min	Service Factor	1
Frame	184T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	73.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	18.0 A	Power Factor	95
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	G
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	55
Number of Speeds	1		


Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Resistance Main	0 O	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005018.01	Outline Drawing	035564-1200

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2025




VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



* THIS LEAD MAY BE WHITE

LINE LEADS



ROTATION
FACING
LEAD END

L1

L2

C.C.W.

T1,T8

T4,T5

C.W.

T1,T5

T4,T8

DRAWING REVISION AD	REVISION BY SB	REV DATE/ © DATE 08/01/2025
REQUEST NUMBER CR-0023654	APPROVED BY SBD	DATE 08/01/2025
REQUEST NUMBER DESCRIPTION DRAWING TITLE BLOCK UPDATED		
COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.		

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY ADH
DATE 02/19/74
APPROVED BY JCW
DATE 02/20/74
REFERENCE
THIRD ANGLE PROJECTION



marathon™			
DESCRIPTION EXTERNAL WIRING DIAGRAM TYPE "K" W/O PROTECTOR			
MATERIAL DECAL - 004018		PROCESS/FINISH	
SIZE A	DRAWING NUMBER 005018-01		SHEET 1 OF 1
4 of 4			