

PRODUCT INFORMATION PACKET



Model No: G140281.00

Catalog No: G140281.00

DISCONTINUED - REPLACED BY 140820.00 - 10HP..1760/1450RPM.215.TEFC.208-230/460V.3PH.60/50HZ.CONT.NOT.40
C.1.15/1.15SF.RIGID.WASHGUARD.C215T17WB3D



Nameplate Specifications


Technical Specifications

Outline Drawing	037620-1150	Connection Drawing	005010.01
-----------------	-------------	--------------------	-----------


This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/19/2025



VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



LINE LEADS



VOLTAGE	L1	L2	L3	JOIN & INSULATE
HIGH	T1	T2	T3	(T4,T7) (T5,T8) (T6,T9)
LOW	T1,T7	T2,T8	T3,T9	T4,T5,T6

DRAWING REVISION F	REVISION BY SB	REV DATE/© DATE 08/01/2025
REQUEST NUMBER CR-0023654	APPROVED BY SBD	DATE 08/01/2025
REQUEST NUMBER DESCRIPTION DRAWING TITLE BLOCK UPDATED		
COPYRIGHT (PER REVISION DATE) MARATHON ELECTRIC, LLC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF MARATHON ELECTRIC, LLC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.		

PRIMARY DIMENSIONS ARE INCH
mm DIMENSIONS IN [BRACKETS]
ARE FOR REFERENCE ONLY

DRAWN BY RDW
DATE 04/12/02
APPROVED BY
DATE
REFERENCE
THIRD ANGLE PROJECTION

marathon™

DESCRIPTION
EXTERNAL WIRING DIAGRAM
3 PHASE W/O PROTECTOR

MATERIAL		PROCESS/FINISH	
DECAL - 004014			
SIZE	DRAWING NUMBER		SHEET
A	005010-01		1 OF 1