

# PRODUCT INFORMATION PACKET



Model No: T10082-8  
Catalog No: T10082-8  
10-24 SEMS SCREW

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



## Nameplate Specifications

## Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/05/2025

PART NO.	SIZE & THREADS	LENGTH	FINISH	TYPE OF WASHER	TYPE OF HEAD	MISC.
T-10082-3	# 10-24	.50	N.A.	EXTERNAL	PAN	
T-10082-4	# 10-24	.38	N.A.	EXTERNAL	PAN	
T-10082-5	# 10-24	.75	N.A.	EXTERNAL	PAN	
T-10082-6	SUPERSEDED BY T9695-1 & CF000335					
T-10082-8	# 10-24	1.12	N.A.	EXTERNAL	PAN	
T-10082-12	# 6-24	.25	N.A.	EXTERNAL	PAN HD. PHILLIPS	
T-10082-13	# 10-24	.44	N.A.	C*SUNK	FLAT	
T-10082-14	1/4-20	.50	N.A.	KANTLINK	FILLISTER	
T-10082-20	1/4-20	.50	N.A.	KANTLINK	PAN	
T-10082-21	1/4-20	.38	N.A.	KANTLINK	PAN	
T-10082-22	OBSOLETE PER CRM 22947					
T-10082-23	1/4-20	.62	N.A.	EXTERNAL	HEX	
T-10082-25	OBSOLETE PER CRM 22947					
T-10082-26	5/16-18	.62	N.A.	EXTERNAL	N.C.	
T-10082-27	# 8-32	.31	N.A.	EXTERNAL	ROUND HD PHILLIPS	
T-10082-28	5/16-18	.75	N.A.	KANTLINK	N.C.	
T-10082-29	# 10-24	.50	N.A.	KANTLINK	PAN HD. PHILLIPS	
T-10082-30	# 6-32	.31	N.D	EXTERNAL	PAN HD. PHILLIPS	

NOTE: PHILLIPS HEAD ONLY WHEN SPECIFIED.

FOR PARTS ORDERS SEND:

{1} 3/8-16 X 1.00 HEX HEAD SCREW  
{1} E106A-16 LOCK WASHER

MATERIAL: MILD STEEL UNLESS OTHERWISE SPECIFIED  
TEETH ON "SHAKEPROOF" LOCKWASHERS ARE TO HAVE BOTH EDGES SHARP.

N.A. PLATE PER E-1817 OR E1817-1.

N.B. PLATE PER E-1427.

N.C. HEX HD. (STANDARD, INDENTED OR SLOTTED)


N.D. COAT PER E3147.

BUY

UNLESS OTHERWISE SPECIFIED TOLERANCE  
ON HOLE SIZES PER E2056  
MATERIAL TOLERANCE ("+"") TO AGREE WITH PUBLISHED STANDARDS.

ON 2 PLACE DECIMALS IS ±.02  
ON 3 PLACE DECIMALS IS ±.002  
ON ALL ANGLES IS ±.5 OF A DEGREE

THIS SHEET CONTAINS PROPRIETARY INFORMATION OWNED BY LINCOLN MOTORS AND IS NOT TO BE REPRODUCED, DISCLOSED OR USED WITHOUT THE EXPRESS PERMISSION OF LINCOLN MOTORS

2	02-23-2001	REDRAWN IN ANVIL, REVISED FINISH N.B. TO N.A. CN 30458	BJW		DRAWN BY	BJW	02-23-2001	EQUIP. TYPE	MISC. USE
1	07-23-1999	CHANGE SHEET, 01-15-1999 B 04-01-1999 D, 07-23-1999 G			CHECKED BY	ML	02-23-2001	SUBJECT	SEMS SCREW
REV	DATE	CHANGE	NAME		APPR BY	GK	02-23-2001	MAT. SPEC.	
					SCALE		REF.	SHT. NO.	T 10082

PURCHASED      DISTRIBUTION - WA - LB - WP - LN - BY      CADD FILE NO.      T10082