

PRODUCT INFORMATION PACKET

Model No: 120554.00

Catalog No: 120554.00

Air Compressor Motor, 5 HP, 1 Ph, 60 Hz, 230 V, 3600 RPM, 145T Frame, DP



Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications

Output HP	5 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	230 V
Current	20.8 A	Speed	3450 rpm
Service Factor	1	Phase	1
Efficiency	82.5 %	Power Factor	95
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	E
Frame	145T	Enclosure	Drip Proof
Thermal Protection	Manual	Ambient Temperature	40 °C
Drive End Bearing Size	6205	Opp Drive End Bearing Size	6203
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Selective Clockwise
Resistance Main	.52 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	13.20 in
Frame Length	8.00 in	Shaft Diameter	0.875 in
Shaft Extension	2.25 in	Assembly/Box Mounting	F1 ONLY
Outline Drawing	028588	Connection Drawing	005056.03

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/08/2022



				TOLERANCES UNLESS SPECIFIED			
				DEC	INCHES		
				X	± 1		
02	CHANGED TO MYLAR NAMEPLATE, UPDATED TO CURRENT DESIGN & REDRAWN IN SOLIDWORKS PER ISAAC 11-0954	SAD 3/2/2011	GWS	XX	$\pm .03$	TITLE OUTLINE - 140T FRAME	
				XXX	$\pm .005$	DRIP PROOF - RIGID	
01	ADDED CONNECTION DECAL NOTE TO MATCH BOM	BJB 9/13/04	XXX	XX	$\pm .0005$	MAT'L	
NO	REVISION	BY & DATE	CHK	ANG	$\pm 1/2^\circ$	FINISH	
				RFP	PREV		
				NETWORK FILE NAME 028588		SIZE B	DRAWING NO 028588
						PAGE 02	REV 02



ELECTRIC MOTORS
GEARMOTORS
AND DRIVES

DRAWN RDW 06/15/04

CHK

APPR SW 6/15/04

SCALE 1:2

REF 033389



FMF

PAGE OF

REV

02

VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



ROTATION FACING LEAD END	L1	L2	JOIN
C.C.W.	P1	T4,T5	T1,T8
C.W.	P1	T4,T8	T1,T5

* THIS LEAD MAY BE WHITE

				TOLERANCES UNLESS SPECIFIED		 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN WLW 08/30/76			
				DEC.	INCHES		CHK WRK 09/24/76			
				.X	±.1		APPD			
08	ALTERNATE T5 LEAD MARKING WAS RED	RLW 8/6/02		.XX	±.01	TITLE EXTERNAL WIRING DIAGRAM TYPE "K" W/ PROTECTOR		SCALE 1=1		
07	ADDED ALTERNATE T5 LEAD MARKING	RLW 5/31/02	KH	.XXX	±.005			REF		
06	REDRAWN TO CAD	DBT 5/31/02		.XXXX	±.0005	MAT'L. DECAL – 004015		FMF 6K17FB4		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH		PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP		CAD FILE 00505603		SIZE	DRAWING NO.		REV.
			DIST BRF–NLV				A	005056–03		08



**1051 CHEYENNE AVE.
GRAFTON, WI 53024
PH. 262-377-8810**

CERTIFICATION DATA SHEET

CONN. DIAGRAM: 005056.03
OUTLINE: 028588
WINDING #: K632130 DR 2 A

CATALOG #: 120554.00
MOUNTING: F1 ONLY

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
5	3.70	3600	3450	145T	DP	E	L

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
1	60	230	20.8	ACROSS THE LINE	CONTINUOUS	F4	1.0	40

FULL LOAD EFF:	82.5	3/4 LOAD EFF:	83.8	1/2 LOAD EFF:	82.8	GTD. EFF		ELEC. TYPE
FULL LOAD PF:	95	3/4 LOAD PF:	93.8	1/2 LOAD PF:	91.4	80		CAP START CAP RUN

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
7.5 LB-FT	107	12.3 LB-FT 164 %	14.3 LB-FT 191 %	105

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS / HOUR	APPROX. MOTOR WGT
0 dBA	10 dBA	0.095 LB-FT^2	0.1 LB-FT^2	10 SEC.	0	49 LBS.

***** SUPPLEMENTAL INFORMATION *****

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE - LEESON (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL						
6205	6203						
		POLYREX EM	T	VERIFY	VERIFY	1144 STRESSPROOF (C-223)	ROLLED STEEL

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	MANUAL	NONE	NONE	NONE	FALSE	NONE VOLTS

*

N

O

T

E

S

*

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE
ENCODER: NONE NONE NONE NONE NONE PPR
BRAKE: NONE NONE NONE P/N NONE NONE NONE NONE FT-LB NONE V NONE Hz



**1051 CHEYENNE AVE.
GRAFTON, WI 53024
PH. 262-377-8810**

CERTIFICATION DATA SHEET

CUSTOMER:
ORDER #:
CONN. DIAGRAM: 005056.03
OUTLINE: 028588
WINDING #: K632130 DR 2 A

CUSTOMER PO#:
CATALOG #:
CUSTOMER PART #:
MOUNTING: F1 ONLY

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
5	3.70	3600	3450	145T	DP	E	L

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
1	60	230	20.8	ACROSS THE LINE	CONTINUOUS	F4	1.0	40

FULL LOAD EFF:	82.5	3/4 LOAD EFF:	83.8	1/2 LOAD EFF:	82.8	GTD. EFF		ELEC. TYPE
FULL LOAD PF:	95	3/4 LOAD PF:	93.8	1/2 LOAD PF:	91.4	80		CAP START CAP RUN

F.L. TORQUE		LOCKED ROTOR AMPS		L.R. TORQUE		B.D. TORQUE		F.L. RISE°C
9.8 LB-FT		107		12.3 LB-FT 164 %		14.3 LB-FT 191 %		105

SOUND PRESSURE @ 3 FT.		SOUND POWER		ROTOR WK^2		MAX. WK^2		SAFE STALL TIME		STARTS / HOUR		APPROX. MOTOR WGT
0 dBA		10 dBA		0.095 LB-FT^2		0.1 LB-FT^2		10 SEC.		0		0 LBS.

***** SUPPLEMENTAL INFORMATION *****

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE - LEESON (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL						
6205	6203						
		POLYREX EM	T	VERIFY	VERIFY	1144 STRESSPROOF (C-223)	ROLLED STEEL

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	MANUAL	NONE	NONE	NONE	FALSE	NONE VOLTS

*

N

O

T

E

S

*

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

PREPARED BY: Dinesh
Suddula **DATE:**
02/22/2019 02:25:58 AM
FORM 3531 REV.3 02/07/99
** Subject to change without
notice.



**1051 CHEYENNE AVE.
GRAFTON, WI 53024
PH. 262-377-8810**

CERTIFICATION DATA SHEET

CUSTOMER:
ORDER #:
CONN. DIAGRAM: 005056.03
OUTLINE: 028588
WINDING #: K632130 DR 2 A

CUSTOMER PO#:
CATALOG #:
CUSTOMER PART #:
MOUNTING: F1 ONLY

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
5	3.70	3600	3450	145T	DP	E	L

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
1	60	230	20.8	ACROSS THE LINE	CONTINUOUS	F4	1.0	40

FULL LOAD EFF:	82.5	3/4 LOAD EFF:	83.8	1/2 LOAD EFF:	82.8	GTD. EFF		ELEC. TYPE
FULL LOAD PF:	95	3/4 LOAD PF:	93.8	1/2 LOAD PF:	91.4	80		CAP START CAP RUN

F.L. TORQUE		LOCKED ROTOR AMPS		L.R. TORQUE		B.D. TORQUE		F.L. RISE°C
7.5 LB-FT		107		12.3 LB-FT 164 %		14.3 LB-FT 191 %		105

SOUND PRESSURE @ 3 FT.		SOUND POWER		ROTOR WK^2		MAX. WK^2		SAFE STALL TIME		STARTS / HOUR		APPROX. MOTOR WGT
0 dBA		10 dBA		0.095 LB-FT^2		0.1 LB-FT^2		10 SEC.		0		0 LBS.

***** SUPPLEMENTAL INFORMATION *****

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE - LEESON (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL	POLYREX EM	T	VERIFY	VERIFY	1144 STRESSPROOF (C-223)	ROLLED STEEL
6205	6203						

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	MANUAL	NONE	NONE	NONE	FALSE	NONE VOLTS

*

N

O

T

E

S

*

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

PREPARED BY: Dinesh
Suddula **DATE:**
02/22/2019 02:25:58 AM
FORM 3531 REV.3 02/07/99
** Subject to change without
notice.



**1051 CHEYENNE AVE.
GRAFTON, WI 53024
PH. 262-377-8810**

CERTIFICATION DATA SHEET

CUSTOMER:
ORDER #:
CONN. DIAGRAM: 005056.03
OUTLINE: 028588
WINDING #: K632130 DR 2 A

CUSTOMER PO#:
CATALOG #:
CUSTOMER PART #:
MOUNTING: F1 ONLY

TYPICAL MOTOR PERFORMANCE DATA

HP	kW	SYNC. RPM	F.L. RPM	FRAME	ENCLOSURE	KVA CODE	DESIGN
5	3.70	3600	3450	145T	DP	E	L

PH	Hz	VOLTS	AMPS	START TYPE	DUTY	INSL	S.F.	AMB°C
1	60	230	20.8	ACROSS THE LINE	CONTINUOUS	F4	1.0	40

FULL LOAD EFF:	82.5	3/4 LOAD EFF:	83.8	1/2 LOAD EFF:	82.8	GTD. EFF		ELEC. TYPE
FULL LOAD PF:	95	3/4 LOAD PF:	93.8	1/2 LOAD PF:	91.4	80		CAP START CAP RUN

F.L. TORQUE	LOCKED ROTOR AMPS	L.R. TORQUE	B.D. TORQUE	F.L. RISE°C
9.8 LB-FT	107	12.3 LB-FT 164 %	14.3 LB-FT 191 %	105

SOUND PRESSURE @ 3 FT.	SOUND POWER	ROTOR WK^2	MAX. WK^2	SAFE STALL TIME	STARTS / HOUR	APPROX. MOTOR WGT
0 dBA	10 dBA	0.095 LB-FT^2	0.1 LB-FT^2	10 SEC.	0	0 LBS.

***** SUPPLEMENTAL INFORMATION *****

DE BRACKET TYPE	ODE BRACKET TYPE	MOUNT TYPE	ORIENTATION	SEVERE DUTY	HAZARDOUS LOCATION	DRIP COVER	SCREENS	PAINT
STANDARD	STANDARD	RIGID	HORIZONTAL	FALSE	NONE	FALSE	NONE	BLUE - LEESON (ENAMEL)

BEARINGS		GREASE	SHAFT TYPE	SPECIAL DE	SPECIAL ODE	SHAFT MATERIAL	FRAME MATERIAL
DE	ODE						
BALL	BALL						
6205	6203						
		POLYREX EM	T	VERIFY	VERIFY	1144 STRESSPROOF (C-223)	ROLLED STEEL

THERMO-PROTECTORS				THERMISTORS	CONTROL	SPACE HEATERS
THERMOSTATS	PROTECTORS	WDG RTDs	BRG RTDs			
NONE	MANUAL	NONE	NONE	NONE	FALSE	NONE VOLTS

*

N

O

T

E

S

*

INVERTER TORQUE: NONE
INV. HP SPEED RANGE: NONE

ENCODER: NONE
NONE NONE
NONE NONE PPR

BRAKE: NONE NONE
NONE P/N NONE
NONE NONE
NONE FT-LB NONE V NONE Hz

PREPARED BY: Dinesh
Suddula **DATE:**
02/22/2019 02:25:58 AM
FORM 3531 REV.3 02/07/99
** Subject to change without
notice.


Model No 120554.00Catalog No 120554.00

LEESON ELECTRIC CORPORATION

TYPICAL PERFORMANCE CURVE for AC MOTOR

Curve at 230
60
5

Volts
HZ
HP

HP 5.00VOLTS 230HZ 60PHASE 1RPM 3450

FL TORQUE 7.5 Lb.Ft
BD TORQUE 14.3 Lb.Ft
LR TORQUE 12.3 Lb.Ft

WINDING K632130-2

FL AMPS 20.8
PU TORQUE 13.3 Lb.Ft
LR AMPS 107

Date 3/16/2018