

### Nameplate Specifications

Phase	3	Output HP	3 & 3 Hp
Output KW	2.2 & 2.2 kW	Voltage	230/460 & 200/400 V
Speed	1755 & 1450 rpm	Service Factor	1.15 & 1.0
Frame	100L	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	88.5 & 86.5 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	8/4 & 9.2/4.6 A	Power Factor	79.5
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	J
Drive End Bearing Size	NONE	Opp Drive End Bearing Size	NONE
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

### Technical Specifications

Electrical Type	Squirrel Cage Inverter Rated	Starting Method	Line Or Inverter
Poles	4	Rotation	Reversible
Resistance Main	3.58 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Cast Iron
Shaft Type	IEC	Overall Length	17.12 in
Shaft Diameter	1.111 in	Shaft Extension	2.36 in
Assembly/Box Mounting	F3		
Connection Drawing	00546501ME	Outline Drawing	SS620006-100L