

PRODUCT INFORMATION PACKET



Model No: 93445-60
Catalog No: 93445-60
A-93445-60 SGR (BOLT-THRU) 2.771-2.810 SH/3.294 BC

Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2025 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications


Technical Specifications

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:04/05/2025

93445 KIT INCLUDES:

- A - (1) SHAFT GND. RING
 B - (2) M3 x .5 x 14 CAP SCREWS *
 C - (2) M3 SPLIT LOCKWASHERS *

* SGR OD'S OVER 4.60"
 WILL USE (4) MTG. SCREWS.



DASH	MIN. SHAFT DIA. INCHES	MAX. SHAFT DIA. INCHES	OUTSIDE DIA. INCHES ±.02	THICKNESS INCHES	SGR PART NUMBER	BOLT CIRCLE	ITEM REV.
1	.311	.355	1.60	.295	SGR-6.9-3	1.200	01
2							
3	.356	.395	1.60	.295	SGR-8.0-3	1.200	02
4	.396	.435	1.60	.295	SGR-9.0-3	1.200	02
5	.436	.480	1.60	.295	SGR-10.1-3	1.200	02
6	.481	.520	1.60	.295	SGR-11.2-3	1.200	02
7	.521	.560	1.60	.295	SGR-12.2-3	1.200	02
8	.561	.605	1.60	.295	SGR-13.2-3	1.200	02
9	.606	.645	1.60	.295	SGR-14.4-3	1.200	02
10	.646	.685	2.10	.295	SGR-15.4-3	1.783	02
11	.686	.730	2.10	.295	SGR-16.4-3	1.783	02
12	.731	.774	2.10	.295	SGR-17.6-3	1.783	02
13	.775	.815	2.10	.295	SGR-18.7-3	1.783	02
14	.816	.855	2.10	.295	SGR-19.7-3	1.783	02
15	.856	.895	2.10	.295	SGR-20.7-3	1.783	02
16	.896	.935	2.10	.295	SGR-21.7-3	1.783	02
17	.936	.980	2.10	.295	SGR-22.8-3	1.783	02
18	.981	1.020	2.10	.295	SGR-23.9-3	1.783	02
19	1.021	1.060	2.10	.295	SGR-24.9-3	1.783	02
20	1.061	1.105	2.10	.295	SGR-25.9-3	1.783	02
21	1.106	1.145	2.10	.295	SGR-27.1-3	1.783	02
22	1.146	1.185	2.10	.295	SGR-28.1-3	1.783	02
23	1.231	1.270	2.10	.295	SGR-30.3-3	1.783	01
24	1.271	1.310	2.10	.295	SGR-31.3-3	1.783	01
25	1.311	1.355	2.10	.295	SGR-32.3-3	1.783	01
26	1.356	1.395	2.10	.295	SGR-33.4-3	1.783	01
27	1.396	1.435	2.68	.295	SGR-34.4-3	2.433	01
28	1.436	1.480	2.68	.295	SGR-35.5-3	2.433	01
29	1.481	1.520	2.68	.295	SGR-36.6-3	2.433	01
30	1.521	1.560	2.68	.295	SGR-37.6-3	2.433	01
31	1.561	1.605	2.68	.295	SGR-38.6-3	2.433	01
32	1.606	1.645	2.68	.295	SGR-39.8-3	2.433	01
33	1.646	1.685	2.68	.295	SGR-40.8-3	2.433	01
34	1.686	1.730	2.68	.295	SGR-41.8-3	2.433	01
35	1.731	1.770	2.68	.295	SGR-43.0-3	2.433	01
36	1.771	1.810	2.68	.295	SGR-44.0-3	2.433	01
37	1.811	1.855	2.68	.295	SGR-45.0-3	2.433	01
38	1.856	1.895	2.68	.295	SGR-46.1-3	2.433	01
39	1.896	1.935	2.68	.295	SGR-47.1-3	2.433	01
40	1.936	1.980	2.68	.295	SGR-48.2-3	2.433	01
41	1.981	2.020	2.68	.295	SGR-49.3-3	2.433	01
42	2.021	2.060	3.10	.295	SGR-50.3-3	2.783	01
43	2.061	2.105	3.10	.295	SGR-51.3-3	2.783	01
44	2.106	2.145	3.10	.295	SGR-52.5-3	2.783	01
45	2.146	2.185	3.10	.295	SGR-53.5-3	2.783	01
46	2.186	2.230	3.10	.295	SGR-54.5-3	2.783	01
47	2.231	2.270	3.10	.295	SGR-55.7-3	2.783	01
48	2.271	2.310	3.10	.295	SGR-56.7-3	2.783	01
49	2.311	2.355	3.10	.295	SGR-57.7-3	2.783	01
50	2.356	2.395	3.10	.295	SGR-58.8-3	2.783	01
51	2.396	2.435	3.60	.295	SGR-59.8-3	3.294	01
52	2.436	2.480	3.60	.295	SGR-60.9-3	3.294	01
53	2.481	2.520	3.60	.295	SGR-62.0-3	3.294	01
54	2.521	2.560	3.60	.295	SGR-63.0-3	3.294	01
55	2.561	2.605	3.60	.295	SGR-64.0-3	3.294	01
56	2.606	2.645	3.60	.295	SGR-65.2-3	3.294	01

DRAWING REVISION R
 ECO NMR-0208199
 ECO DESCRIPTION

REVISION BY A. KEETHA
 APPROVED BY A. KEETHA

DATE 05-11-2021
 DATE 05-11-2021

ADDED DASH #89

COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED.
 PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES UNLESS OTHERWISE SPECIFIED:
 DEC. INCH mm ANGLE
 .X ±0.1 [±2.5] ±7° 30"
 .XX ±0.02 [±0.51]
 .XXX ±0.005 [±0.127]
 .XXXX ±0.0005 [±0.0127]
 REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.076/381] X 45°
 CORNER FILLETS: R.02 [51]
 MACHINED SURFACES: 200 INCH mm 5.1/
 mm SHOWN IN [BRACKETS]

DRAWN BY JJB
 DATE 04-01-2011
 APPROVED BY MJS
 DATE 04-04-2011
 REFERENCE
 THIRD ANGLE PROJECTION

REGAL™ Regal Beloit America, Inc.




DESCRIPTION
SHAFT GROUNDING RING
 SGR BRUSH ASSY - BOLT THROUGH

MATERIAL PROCESS/FINISH
 SIZE A DRAWING NUMBER 93445 SHEET 1 OF 2

93445 KIT INCLUDES:

- A - (1) SHAFT GND. RING
B - (2) M3 x .5 x 14 CAP SCREWS *
C - (2) M3 SPLIT LOCKWASHERS *

* SGR OD'S OVER 4.60"
WILL USE (4) MTG. SCREWS.



DASH	MIN. SHAFT DIA. INCHES	MAX. SHAFT DIA. INCHES	OUTSIDE DIA. INCHES ±.02	THICKNESS INCHES	SGR PART NUMBER	BOLT CIRCLE	ITEM REV.
57	2.646	2.685	3.60	.295	SGR-66.2-3	3.294	01
58	2.686	2.730	3.60	.295	SGR-67.2-3	3.294	01
59	2.731	2.770	3.60	.295	SGR-68.4-3	3.294	01
60	2.771	2.810	3.60	.295	SGR-69.4-3	3.294	01
61	2.811	2.855	3.60	.295	SGR-70.4-3	3.294	01
62	2.856	2.895	3.60	.295	SGR-71.5-3	3.294	01
63	2.896	2.935	4.10	.295	SGR-72.5-3	3.806	01
64	2.936	2.980	4.10	.295	SGR-73.6-3	3.806	01
65	2.981	3.020	4.10	.295	SGR-74.7-3	3.806	01
66	3.021	3.060	4.10	.295	SGR-75.7-3	3.806	01
67	3.061	3.105	4.10	.295	SGR-76.7-3	3.806	01
68	3.106	3.145	4.10	.295	SGR-77.9-3	3.806	01
69	3.146	3.185	4.10	.295	SGR-78.9-3	3.806	01
70	3.186	3.230	4.10	.295	SGR-79.9-3	3.806	01
71	3.231	3.270	4.10	.295	SGR-81.1-3	3.806	01
72	3.271	3.310	4.10	.295	SGR-82.1-3	3.806	01
73	3.311	3.355	4.10	.295	SGR-83.1-3	3.806	01
74	3.356	3.395	4.10	.295	SGR-84.2-3	3.806	01
75	3.396	3.435	4.60	.295	SGR-85.2-3	4.300	01
76	3.436	3.480	4.60	.295	SGR-86.3-3	4.300	01
77	3.481	3.520	4.60	.295	SGR-87.4-3	4.300	01
78	3.521	3.560	4.60	.295	SGR-88.4-3	4.300	01
79	3.561	3.605	4.60	.295	SGR-89.4-3	4.300	01
80	3.606	3.645	4.60	.295	SGR-90.6-3	4.300	01
81	3.646	3.685	4.60	.295	SGR-91.6-3	4.300	01
82	3.686	3.730	4.60	.295	SGR-92.6-3	4.300	01
83	3.731	3.770	4.60	.295	SGR-93.8-3	4.300	01
84	3.771	3.810	4.60	.295	SGR-94.8-3	4.300	01

DASH	MIN. SHAFT DIA. INCHES	MAX. SHAFT DIA. INCHES	OUTSIDE DIA. INCHES ±.02	THICKNESS INCHES	SGR PART NUMBER	BOLT CIRCLE	ITEM REV.
85	3.811	3.855	4.60	.295	SGR-95.8-3	4.300	01
86							
87							
88	3.936	3.980	5.10	.295	SGR-99.0-3	4.783	01
89	3.981	4.020	5.10	.295	SGR-100.1-3	4.783	01
90							
91							
92	4.106	4.145	5.10	.295	SGR-103.3-3	4.783	01
93							
94							
95	4.231	4.270	5.10	.295	SGR-106.5-3	4.783	01
96	4.275	4.311	5.10	.295	SGR-107.5-3	4.783	00
97							
98	4.356	4.395	5.10	.295	SGR-109.63	4.783	00
99							
100							
101	4.481	4.520	5.60	.295	SGR-112.8-3	5.282	02
102							
103							
104							
105							
106							
107							
108							
109	4.811	4.855	5.60	.295	SGR-121.2-3	5.282	01
120	5.271	5.310	6.10	.295	SGR-132.9-3	5.783	01
121	1.186	1.230	2.10	.295	SGR-29.1-3	1.783	01

DRAWING REVISION R
REVISION BY A. KEETHA
DATE 05-11-2021

ECO NMR-0208199
APPROVED BY A. KEETHA
DATE 05-11-2021

ECO DESCRIPTION
ADDED DASH #89

COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED.
PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.

TOLERANCES UNLESS OTHERWISE SPECIFIED:
DEC. INCH mm ANGLE
.X ±0.1 [±2.5] ±7' 30"
.XX ±0.02 [±0.51]
.XXX ±0.005 [±0.127]
.XXXX ±0.0005 [±0.0127]
REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [.076/.381] X 45°
CORNER FILLETS: R.02 [.51]
MACHINED SURFACES: 200 INCH 5.1/mm
mm SHOWN IN [BRACKETS]

DRAWN BY JJB
DATE 04-01-2011

APPROVED BY MJS
DATE 04-04-2011

REFERENCE

THIRD ANGLE PROJECTION



Regal Beloit America, Inc.

DESCRIPTION
SHAFT GROUNDING RING
SGR BRUSH ASSY - BOLT THROUGH

MATERIAL PROCESS/FINISH

SIZE A DRAWING NUMBER 93445 SHEET 2 OF 2