

PRODUCT INFORMATION PACKET

marathon®
Motors

Model No: 1009067-BR

Catalog No: 1009067

TerraMAX® Cast Iron Motor, 1.50 HP, 3 Ph, 60 Hz, 380 V, 1800 RPM, 80M2 Frame, TEFC



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord

Nameplate Specifications

Output HP	1.50 Hp	Output KW	1.1 kW
Frequency	60 Hz	Voltage	380 V
Current	6.7 A	Speed	1731 rpm
Service Factor	1.25	Phase	3
Efficiency	85 %	Power Factor	0.77
Duty	S1	Insulation Class	F
Frame	80M2	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6204	Opp Drive End Bearing Size	6204
UL	No	CSA	No
CE	No	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise
Mounting	B3	Motor Orientation	Horizontal
Drive End Bearing	Zz C3	Opp Drive End Bearing	Zz C3
Frame Material	Cast	Shaft Type	Keyed
Overall Length	306 mm	Frame Length	165 mm
Shaft Diameter	19 mm	Shaft Extension	40 mm
Assembly/Box Mounting	TOP		
Outline Drawing	0208000334		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022

4




3

Uncontrolled Copy


2

1

OUTLINE



DRAWING REVISION B	REVISION BY NIV	DATE 20/09/2017
ECO ECO-0131516	APPROVED BY JAY	DATE 20/09/2017
ECO DESCRIPTION		
UPDATED DRAWING		
COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.		



DRAWN BY NIV	marathon™ Motors		
DATE 17/07/2017			
APPROVED BY JAY	DESCRIPTION		
DATE 17/07/2017	80 FR- B3 MTG. MOTOR TYPE TCA / QCA		
REFERENCE	MATERIAL	PROCESS/FINISH	
THIRD ANGLE PROJECTION	SIZE B	DRAWING NUMBER 0208000334	SHEET 1 OF 1

4


3

2

1

FORM 14
FORM #6064

BROWNING MANUFACTURING COMPANY, MAYSVILLE, KENTUCKY		12 245						
DATE 1-15-68	4TC72 CAST IRON SHEAVE	Material - 4TC70-72 CSTG.						
DR. S. Y. JR.		Carton - T84						
CHK'D <i>SA</i>	Mfg. Data	Balance - 1/4 oz.						
DISTRIBUTION		Finish - STD. GRAY						
REVISION	BY	DATE	REVISION	BY	DATE	REVISION	BY	DATE
A ADD DRILL DEPTH & GROOVE LOC.	AD	9-6-68	D FIN. BACK SIDE HUB ECO83-133E	RT	5-26-83			
B CSTG. WAS 4TC72	AD	7-1-69	E ECO91-759	KH	4-92			
C Revised Per CR74-170	JH	9/74	F ECO#03-018	KH	3/4/03			

DWG. NO. ~~68X9135-4~~

41009067

Issue
F


Model No. 1009067

Enclosure	U (V)	Δ / Y Conn	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [kgm]	T [Nm]	IE Class	Amb [°C]	Duty	Elevation [m]	Inertia [kg-m ²]	Weight [kg]
TEFC	380	Δ	60	1.1	2	2.6	1731	0.62	6.08	IR3	40	S1	1000	0.0104	23

Motor Load Data

Load Point		NL	1/4FL	1/2FL	3/4FL	FL	5/4FL
Current	A	1.3	1.4	1.7	2.1	2.6	3.1
Torque	Nm	0.0	1.5	3.0	4.6	6.1	7.8
Speed	r/min	1800	1782	1767	1749	1731	1708
Efficiency	%	0.0	66.5	83.0	85.2	85.0	83.7
Power Factor	%	10.0	39.5	58.0	69.5	77.0	80.4


Performance vs Load Chart



Motor Speed Torque Data

Load Point		LR	P-Up	BD	Rated	NL
Speed	r/min	0	164	1367	1731	1800
Current	A	17.2	15.4	9.0	2.6	1.3
Torque	pu	3.0	2.5	2.8	1	0

Starting Characteristics Chart



NOTE Refer data sheet for applicable standard and tolerances on performance parameters

Issued By

Issued Date