

# PRODUCT INFORMATION PACKET

**marathon®**  
Motors

Model No: 1009072-BR

Catalog No: 1009072

TerraMAX® Cast Iron Motor, 15 HP, 3 Ph, 60 Hz, 380 V, 1800 RPM, 132S/M Frame, TEFC



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

**RegalRexnord**


## Nameplate Specifications

Output HP	15 Hp	Output KW	11.0 kW
Frequency	60 Hz	Voltage	380 V
Current	7.0 A	Speed	1763 rpm
Service Factor	1.25	Phase	3
Efficiency	92.4 %	Power Factor	0.79
Duty	S1	Insulation Class	F
Frame	132S/M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6308	Opp Drive End Bearing Size	6208
UL	No	CSA	No
CE	No	IP Code	55
Number of Speeds	1		

## Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	4	Rotation	Clockwise
Mounting	B3	Motor Orientation	Horizontal
Drive End Bearing	Zz C3	Opp Drive End Bearing	Zz C3
Frame Material	Cast	Shaft Type	Keyed
Overall Length	503 mm	Frame Length	240 mm
Shaft Diameter	38 mm	Shaft Extension	80 mm
Assembly/Box Mounting	TOP		
Outline Drawing	0213200587		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022




Model No. 1009072

Enclosure	U (V)	Δ / Y Conn	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [kgm]	T [Nm]	IE Class	Amb [°C]	Duty	Elevation [m]	Inertia [kg-m <sup>2</sup> ]	Weight [kg]
TEFC	380	Δ	60	11	15	23.0	1763	6.09	59.68	IR3	40	S1	1000	0.22	94

**Motor Load Data**

Load Point		NL	1/4FL	1/2FL	3/4FL	FL	5/4FL
Current	A	10.9	11.5	14.2	18.5	23.0	28.4
Torque	Nm	0.0	14.9	30.0	45.2	59.7	76.3
Speed	r/min	1800	1791	1783	1773	1763	1751
Efficiency	%	0.0	73.6	91.2	91.8	92.4	91.3
Power Factor	%	5.5	40.9	61.0	73.0	79.0	81.1


**Performance vs Load Chart**



**Motor Speed Torque Data**

Load Point		LR	P-Up	BD	Rated	NL
Speed	r/min	0	360	1371	1763	1800
Current	A	161.0	144.9	116.9	23.0	10.9
Torque	pu	3.0	2.5	3.1	1	0

**Starting Characteristics Chart**



**NOTE** Refer data sheet for applicable standard and tolerances on performance parameters

Issued By

Issued Date