

Nameplate Specifications

Output HP	2 Hp	Output KW	1.5 kW
Frequency	50 Hz	Voltage	220-240 V
Current	11.4 A	Speed	1440 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	H
Frame	182TZ	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Assembly/Box Mounting	F2 ONLY
Outline Drawing	OL130262	Connection Drawing	005018.06

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022