

PRODUCT INFORMATION PACKET

marathon®
Motors

Model No: 1011635-BR

Catalog No: 1011635

TerraMAX® Cast Iron Motor, 125 HP, 3 Ph, 60 Hz, 380 V, 1200 RPM, 280S/M Frame, TEFC



Regal and Marathon are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E

RegalRexnord



Nameplate Specifications




Output HP	125 Hp	Output KW	90.0 kW
Frequency	60 Hz	Voltage	380 V
Current	175.2 A	Speed	1189 rpm
Service Factor	1.25	Phase	3
Efficiency	95 %	Power Factor	0.84
Duty	S1	Insulation Class	F
Frame	280S/M	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6317	Opp Drive End Bearing Size	6317
UL	No	CSA	No
CE	No	IP Code	55
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage	Starting Method	Direct On Line
Poles	6	Rotation	Clockwise
Mounting	B3	Motor Orientation	Horizontal
Drive End Bearing	C3	Opp Drive End Bearing	C3
Frame Material	Cast	Shaft Type	Keyed
Overall Length	1111 mm	Frame Length	600 mm
Shaft Diameter	75 mm	Shaft Extension	140 mm
Assembly/Box Mounting	TOP		
Outline Drawing	0228000589		

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:12/02/2022



DRAWING REVISION E		REVISION BY LK		DATE 17/04/2019			DRAWN BY JOY								
ECO ECO-0165600		APPROVED BY SR		DATE 17/04/2019			DATE 18/07/2014								
ECO DESCRIPTION UPDATED MODEL AS PER NEW 3D STRUCTURE COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.							APPROVED BY SBD		DESCRIPTION OUTLINE 280M-4P-B3 MTG. MOTOR TYPE: TCA/QCA						
							DATE 18/07/2014								
							REFERENCE		MATERIAL			PROCESS/FINISH			
						THIRD ANGLE PROJECTION				SIZE B		DRAWING NUMBER 0228000589		SHEET 1 OF 1	


Model No. 1011635

Enclosure	U (V)	Δ / Y Conn	f [Hz]	P [kW]	P [hp]	I [A]	n [RPM]	T [kgm]	T [Nm]	IE Class	Amb [°C]	Duty	Elevation [m]	Inertia [kg-m ²]	Weight [kg]
TEFC	380	Δ	60	90	125	175.2	1189	75.25	737.94	IR3	40	S1	1000	16.278	838

Motor Load Data

Load Point		NL	1/4FL	1/2FL	3/4FL	FL	5/4FL
Current	A	60.0	70.5	100.3	134.9	175.2	217.7
Torque	Nm	0.0	185.9	372.5	560.0	737.9	938.1
Speed	r/min	1200	1197	1195	1192	1189	1186
Efficiency	%	0.0	76.0	94.2	94.6	95.0	94.6
Power Factor	%	4.8	49.1	72.0	81.0	84.0	84.8


Performance vs Load Chart



Motor Speed Torque Data

Load Point		LR	P-Up	BD	Rated	NL
Speed	r/min	0	240	1094	1189	1200
Current	A	1191.4	1072.2	613.7	175.2	60.0
Torque	pu	2.2	1.8	2.6	1	0

Starting Characteristics Chart



NOTE Refer data sheet for applicable standard and tolerances on performance parameters

Issued By

Issued Date