

Nameplate Specifications

Output HP	2 Hp	Output KW	1.5 kW
Frequency	60 Hz	Voltage	208-240 V
Current	12.4/11.2 A	Speed	1740 rpm
Service Factor	1.15	Phase	1
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	J
Frame	182TZ	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	1.04 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	0.875 in
Assembly/Box Mounting	F2 ONLY		
Outline Drawing	OL130254	Connection Drawing	005018.06

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022