



Nameplate Specifications

Phase	1	Output HP	1.50 & 1.50 Hp
Output KW	1.1 & 1.1 kW	Voltage	115/230 & 110/220 V
Speed	1740 & 1440 rpm	Service Factor	1.15 & 1.15
Frame	JX182TZ	Enclosure	Drip Proof
Thermal Protection	Manual	Efficiency	77 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	13/6.5 & 15.4/7.7 A	Power Factor	97
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	K
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1 ONLY
Outline Drawing	OL131370	Connection Drawing	005053.02

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2023