



Nameplate Specifications

Phase	3	Output HP	5 & 5 Hp
Output KW	3.7 & 3.7 kW	Voltage	230/460 & 190/380 V
Speed	1740 & 1440 rpm	Service Factor	1.15 & 1.15
Frame	182CZ	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Manual	Efficiency	82.5 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	13.4/6.7 & 15.4/7.7 A	Power Factor	85
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	M
UL	No	CSA	N
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	VERIFY
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Single Special Extension
Assembly/Box Mounting	VERIFY		
Outline Drawing	OL131381	Connection Drawing	005020.02

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2023