



Nameplate Specifications

Phase	3	Output HP	3 & 1.50 Hp
Output KW	2.2 & 1.1 kW	Voltage	208-230 & 208-230 V
Speed	1725 & 850 rpm	Service Factor	1.0 & 1.0
Frame	184T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	80 & 74 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	8.7-7.6 & 6.7-6.9 A	Power Factor	85
Duty	Continuous	Insulation Class	F
Design Code	1CT	KVA Code	G
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	14.96 in
Frame Length	9.50 in	Shaft Diameter	1.125 in
Shaft Extension	2.75 in	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	035465-950	Connection Drawing	005148.01