



Nameplate Specifications

Phase	3	Output HP	2 & 1 Hp
Output KW	1.5 & 0.75 kW	Voltage	208-230 & 208-230 V
Speed	1740 & 876 rpm	Service Factor	1.00 & 1.00
Frame	184T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	80 & 68 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	5.8 & 5.7 A	Power Factor	88
Duty	Continuous	Insulation Class	B
Design Code	1CT	KVA Code	H
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	2		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4/8	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Overall Length	13.96 in
Frame Length	8.50 in	Shaft Diameter	1.125 in
Shaft Extension	2.75 in	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	005148.01	Outline Drawing	035325-HX