

## Nameplate Specifications

|                        |               |                            |                             |
|------------------------|---------------|----------------------------|-----------------------------|
| Output HP              | 3 Hp          | Output KW                  | 2.2 kW                      |
| Frequency              | 60 Hz         | Voltage                    | 208-230/460 V               |
| Current                | 9.6/4.8 A     | Speed                      | 1140 rpm                    |
| Service Factor         | 1.15          | Phase                      | 3                           |
| Efficiency             | 81.5 %        | Power Factor               | 72                          |
| Duty                   | Continuous    | Insulation Class           | F                           |
| Design Code            | C             | KVA Code                   | J                           |
| Frame                  | 213TC         | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection | Ambient Temperature        | 40 °C                       |
| Drive End Bearing Size | 6207          | Opp Drive End Bearing Size | 6205                        |
| UL                     | Recognized    | CSA                        | Y                           |
| CE                     | Y             | IP Code                    | 43                          |
| Number of Speeds       | 1             |                            |                             |

## Technical Specifications

|                       |                             |                       |                 |
|-----------------------|-----------------------------|-----------------------|-----------------|
| Electrical Type       | Squirrel Cage Induction Run | Starting Method       | Across The Line |
| Poles                 | 6                           | Rotation              | Reversible      |
| Resistance Main       | 0 Ohms                      | Mounting              | Round           |
| Motor Orientation     | Nan                         | Drive End Bearing     | Ball            |
| Opp Drive End Bearing | Ball                        | Frame Material        | Rolled Steel    |
| Shaft Type            | NAN                         | Assembly/Box Mounting | NAN             |
| Outline Drawing       | 035356-1100                 | Connection Drawing    | 005010.01       |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:07/18/2022