

# PRODUCT INFORMATION PACKET



Model No: 131654.00  
Catalog No: 131654.00  
...182.DP./V.3PH.NONEHZ..NOT.0C..RIGID..N182T00DB2A

Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications



Phase	<b>3</b>	Output HP	<b>0 Hp</b>
Output KW	<b>0.00 kW</b>	Voltage	<b>- V</b>
Frame	<b>GX182T</b>	Enclosure	<b>Drip Proof</b>
Thermal Protection	<b>No Protection</b>	Ambient Temperature	<b>0 °C</b>
Frequency	<b>- Hz</b>	Current	<b>- A</b>
Duty	<b>Continuous</b>	Insulation Class	<b>F</b>
Design Code	<b>NO DESIGN CODE</b>	KVA Code	<b>-</b>
Drive End Bearing Size	<b>6206</b>	Opp Drive End Bearing Size	<b>6205</b>
UL	<b>No</b>	CSA	<b>N</b>
CE	<b>N</b>	IP Code	<b>22</b>
Number of Speeds	<b>1</b>		

### Technical Specifications

Electrical Type	<b>Squirrel Cage Induction Run</b>	Starting Method	<b>Across The Line</b>
Poles	<b>4</b>	Rotation	<b>Reversible</b>
Mounting	<b>Rigid Base</b>	Motor Orientation	<b>Horizontal</b>
Drive End Bearing	<b>Ball</b>	Opp Drive End Bearing	<b>Ball</b>
Frame Material	<b>Rolled Steel</b>	Shaft Type	<b>T</b>
Assembly/Box Mounting	<b>F1 ONLY</b>		
Outline Drawing	<b>035759-800</b>	Connection Drawing	<b>NONE</b>

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/29/2024

035759



ø1.13 KNOCKOUTS  
(3) REQUIRED

DASH NO.	"C"	"AD"
850	12.69	3.00
900	13.19	3.50
950	13.69	4.00
1000	14.19	4.50
1050	14.69	5.00
1100	15.19	5.50
1150	15.69	6.00
1200	16.19	6.50

		TOLERANCES UNLESS SPECIFIED		REGAL™ Regal Beloit America, Inc.		DRAWN	LST	8/11/10
		DEC.	INCHES			CHK		
		.X	±.1			APPD		
		.XX	±.03	TITLE		SCALE	1=2	
		.XXX	±.005	OUTLINE - 180T FRAME DRIP PROOF - RIGID MOUNT		REF		
B	DE & NDE BKT ROTATED TO 45°. AS PER CR-0017346	BBR	11/02/2023	MAT'L		FMF		
NO.	REVISION	BY & DATE	CHK	ANG	FINISH	PREV		
			RFP	CAD FILE	035759	SIZE	DRAWING NO.	REV.
			DIST			B	035759	B

THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT