



### Nameplate Specifications

Phase	3	Output HP	0 Hp
Voltage	UNWOUND V	Frame	184T
Enclosure	Drip Proof	Thermal Protection	No Protection
Ambient Temperature	0 °C	Frequency	- Hz
Current	- A	Duty	Continuous
Insulation Class	F	Design Code	NO DESIGN CODE
KVA Code	-	Drive End Bearing Size	6206
Opp Drive End Bearing Size	6205	UL	No
CSA	N	CE	N
IP Code	22	Number of Speeds	1

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	T
Shaft Diameter	1.125 in	Assembly/Box Mounting	F1 ONLY
Outline Drawing	608-0001-000	Connection Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/29/2024