

# PRODUCT INFORMATION PACKET



Model No: 131655.00  
Catalog No: 131655.00  
...184.DP./V.3PH.NONEHZ..NOT.0C..RIGID..N184T00DB2A

Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E







**Nameplate Specifications**

Phase	<b>3</b>	Output HP	<b>0 Hp</b>
Voltage	<b>UNWOUND V</b>	Frame	<b>184T</b>
Enclosure	<b>Drip Proof</b>	Thermal Protection	<b>No Protection</b>
Ambient Temperature	<b>0 °C</b>	Frequency	<b>- Hz</b>
Current	<b>- A</b>	Duty	<b>Continuous</b>
Insulation Class	<b>F</b>	Design Code	<b>NO DESIGN CODE</b>
KVA Code	<b>-</b>	Drive End Bearing Size	<b>6206</b>
Opp Drive End Bearing Size	<b>6205</b>	UL	<b>No</b>
CSA	<b>N</b>	CE	<b>N</b>
IP Code	<b>22</b>	Number of Speeds	<b>1</b>

**Technical Specifications**

Electrical Type	<b>Squirrel Cage Induction Run</b>	Starting Method	<b>Across The Line</b>
Poles	<b>4</b>	Rotation	<b>Reversible</b>
Mounting	<b>Rigid Base</b>	Motor Orientation	<b>Horizontal</b>
Drive End Bearing	<b>Ball</b>	Opp Drive End Bearing	<b>Ball</b>
Frame Material	<b>Rolled Steel</b>	Shaft Type	<b>T</b>
Shaft Diameter	<b>1.125 in</b>	Assembly/Box Mounting	<b>F1 ONLY</b>
Outline Drawing	<b>608-0001-000</b>	Connection Drawing	<b>NONE</b>

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/29/2024



(3) ø1.13 KNOCKOUTS

GASKETS THROUGHOUT

DASH NO.	"C"	"AD"
800	12.19	2.50
850	12.69	3.00
900	13.19	3.50
950	13.69	4.00
1000	14.19	4.50
1050	14.69	5.00
1100	15.19	5.50
1150	15.69	6.00

		TOLERANCES UNLESS SPECIFIED		REGAL™ Regal Beloit America, Inc.		DRAWN LST 6/4/11	
		DEC.	INCHES			CHK	
		.X	±.1			APPD	
		.XX	±.03	TITLE		SCALE 1=2	
		.XXX	±.005	OUTLINE - 180T FRAME		REF 035325	
		.XXXX	±.0005	DRIP PROOF - RIGID MOUNT		FMF	
C	DE & NDE BKT ROTATED TO 45°. AS PER CR-0017346	BBR	11/06/23	MAT'L	PREV		
NO.	REVISION	BY & DATE	CHK	ANG	FINISH		
			RFP		CAD FILE	608-0001	SIZE
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				DIST			DRAWING NO.
							608-0001
							REV. C