

PRODUCT INFORMATION PACKET



Model No: 131761.00

Catalog No: 131761.00

2HP..1740/1440RPM.182.TEFC./220V.1PH.60/50HZ.CONT.NOT.40C.1.15/1.15SF.RIGID..N182C17FB13B

Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.

©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Phase	1	Output HP	2 & 2 Hp
Output KW	1.5 & 1.5 kW	Voltage	220 & 220 V
Speed	1740 & 1440 rpm	Service Factor	1.15 & 1.15
Frame	182T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	40 °C
Frequency	60 & 50 Hz	Current	10.8 & 11.2 A
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	J
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	No	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Outline Drawing	OL131761	Connection Drawing	005442.01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023



VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.

LINE LEADS

ROTATION FACING LEAD END	L1	L2
C.C.W. ROT.	T1	T4 T5
C.W. ROT.	T1 T5	T4

				TOLERANCES UNLESS OTHERWISE SPECIFIED		LEESON ELECTRIC CORPORATION						
				DECIMALS								
				.00	± .01	DRAWN	SAW 05/25/99	TITLE EXTERNAL WIRING DIAGRAM TYPE "C" W/O PROTECTOR				
				.000	± .005	CH'K'D.						
				.0000	± .0005	APPR.		MAT'L. SINGLE VOLT – DUAL ROTATION DECAL – 080844				
NO.	REVISION			BY	DATE	FRACTIONS	± 1/64					SCALE
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED						ANGLES	± 1/2"	REF.	005278–07	FINISH	SIZE	DRAWING NO.
						INCH/MM		FMF	131761	ESCO	A	005442–01

```
ERROR: syntaxerror  
OFFENDING COMMAND: --nostringval--
```

```
STACK:
```

```
-dictionary-  
-dictionary-  
/Pscript_WinNT_Compat  
-dictionary-
```