



Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	208-240/380-415/440-480 V
Current	24.0-22.0/14.0-13.0/ A	Speed	3541 rpm
Service Factor	1	Phase	3
Efficiency	89.5 %	Power Factor	85.7
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	H
Frame	213TCZ	Enclosure	Open Enclosed
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6207	Opp Drive End Bearing Size	6207
UL	Recognized	CSA	Y
CE	Y	IP Code	10
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Mounting	Round	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Single Special Extension
Shaft Diameter	1.125 in	Assembly/Box Mounting	END
Outline Drawing	OL131768	Connection Drawing	005427.01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/18/2023