

**Nameplate Specifications**

Output HP	<b>0 Hp</b>	Output KW	<b>0.00 KW</b>
Frequency	<b>- Hz</b>	Voltage	<b>UNWOUND V</b>
Current	<b>- A</b>	Phase	<b>3</b>
Power Factor	<b>80</b>	Duty	<b>Continuous</b>
Insulation Class	<b>F</b>	Design Code	<b>NO DESIGN CODE</b>
KVA Code	<b>-</b>	Frame	<b>213T</b>
Enclosure	<b>Totally Enclosed Fan Cooled</b>	Thermal Protection	<b>No Protection</b>
Ambient Temperature	<b>0 °C</b>	Drive End Bearing Size	<b>6207</b>
Opp Drive End Bearing Size	<b>6205</b>	UL	<b>No</b>
CSA	<b>N</b>	CE	<b>N</b>
IP Code	<b>43</b>	Number of Speeds	<b>1</b>

**Technical Specifications**

Electrical Type	<b>Squirrel Cage Induction Run</b>	Starting Method	<b>Across The Line</b>
Poles	<b>4</b>	Rotation	<b>Reversible</b>
Mounting	<b>Rigid Base</b>	Motor Orientation	<b>Horizontal</b>
Drive End Bearing	<b>Ball</b>	Opp Drive End Bearing	<b>Ball</b>
Frame Material	<b>Rolled Steel</b>	Shaft Type	<b>Single Special Extension</b>
Assembly/Box Mounting	<b>F1 ONLY</b>		
Connection Drawing	<b>NONE</b>	Outline Drawing	<b>035420-1150</b>

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022