



Nameplate Specifications

Phase	3	Output HP	0 Hp
Output KW	0.00 kW	Voltage	- V
Frame	GX182T	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	0 °C
Frequency	- Hz	Current	- A
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	-
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	No	CSA	N
CE	N	IP Code	22
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	T
Assembly/Box Mounting	F1 ONLY		
Outline Drawing	035759-800	Connection Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/29/2024