



### Nameplate Specifications

|                        |                |                            |                             |
|------------------------|----------------|----------------------------|-----------------------------|
| Phase                  | 3              | Output HP                  | 3 & 0.75 Hp                 |
| Output KW              | 2.2 & 0.56 kW  | Voltage                    | 575 & 575 V                 |
| Speed                  | 1740 & 850 rpm | Service Factor             | 1.00 & 1.00                 |
| Frame                  | 184T           | Enclosure                  | Totally Enclosed Fan Cooled |
| Thermal Protection     | No Protection  | Efficiency                 | 80 & 74 %                   |
| Ambient Temperature    | 40 °C          | Frequency                  | 60 & 60 Hz                  |
| Current                | 3.2 & 1.45 A   | Power Factor               | 86.3                        |
| Duty                   | Continuous     | Insulation Class           | F                           |
| Design Code            | NO DESIGN CODE | KVA Code                   | J                           |
| Drive End Bearing Size | 6206           | Opp Drive End Bearing Size | 6205                        |
| UL                     | Recognized     | CSA                        | Y                           |
| CE                     | N              | IP Code                    | 43                          |
| Number of Speeds       | 1              |                            |                             |

### Technical Specifications

|                       |                             |                       |                 |
|-----------------------|-----------------------------|-----------------------|-----------------|
| Electrical Type       | Squirrel Cage Induction Run | Starting Method       | Across The Line |
| Poles                 | 4                           | Rotation              | Reversible      |
| Resistance Main       | 0 Ohms                      | Mounting              | Rigid Base      |
| Motor Orientation     | Horizontal                  | Drive End Bearing     | Ball            |
| Opp Drive End Bearing | Ball                        | Frame Material        | Rolled Steel    |
| Shaft Type            | T                           | Assembly/Box Mounting | F1 ONLY         |
| Outline Drawing       | 035325-900                  | Connection Drawing    | EE7324          |

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/12/2024