



### Nameplate Specifications

Phase	3	Output HP	3 & 2.50 Hp
Output KW	2.2 & 1.9 kW	Voltage	208-230/460 & 208-230/460 V
Speed	1740 & 1440 rpm	Service Factor	1.15 & 1.15
Frame	182TY	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Efficiency	84 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	8.8/4.4 & 11/5.5 A	Power Factor	76
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	K
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

### Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Round	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Single Special Extension
Assembly/Box Mounting	F1 ONLY		
Outline Drawing	OL131812	Connection Drawing	005010.01

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/22/2023