



Nameplate Specifications

Output HP	5 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	240/480 V
Current	13.0/6.5 A	Speed	1760 rpm
Service Factor	1.15	Phase	3
Efficiency	87.5 %	Power Factor	80
Duty	Continuous	Insulation Class	H
Design Code	B	KVA Code	L
Frame	184TC	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Ambient Temperature	50 °C
Drive End Bearing Size	6207	Opp Drive End Bearing Size	6206
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	2.16 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F2 ONLY
Connection Drawing	005010.01	Outline Drawing	OL131920

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/30/2023