

### Nameplate Specifications

Output HP	7.50 Hp	Output KW	5.6 kW
Frequency	60 Hz	Voltage	240 V
Current	32.4 A	Speed	1725 rpm
Service Factor	1	Phase	1
Efficiency	81.5 %	Power Factor	87
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	F
Frame	184T	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	No	CSA	N
CE	N	IP Code	22
Number of Speeds	1		

### Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Fixed Clockwise
Resistance Main	.347 Ohms	Mounting	PARTIAL MOTOR
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Connection Drawing	005509.01	Outline Drawing	OL132120

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/10/2022