



### Nameplate Specifications

Output HP	7.50 Hp	Output KW	5.6 kW
Frequency	60 Hz	Voltage	220 V
Current	37.0 A	Speed	3450 rpm
Service Factor	1	Phase	1
Efficiency	80 %	Power Factor	85.9
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	D
Frame	184TCZ	Enclosure	Open Enclosed
Thermal Protection	No Protection	Ambient Temperature	55 °C
Drive End Bearing Size	6207	Opp Drive End Bearing Size	6207
UL	Recognized	CSA	Y
CE	Y	IP Code	10
Number of Speeds	1		

### Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	2	Rotation	Fixed Clockwise
Resistance Main	0 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1 ONLY		
Connection Drawing	005368.05	Outline Drawing	OL132143

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/18/2023