



Nameplate Specifications

Phase	3	Output HP	3 Hp
Output KW	2.2 kW	Voltage	480 V
Speed	1765 rpm	Service Factor	1.15
Frame	182TZ	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	Thermostat	Efficiency	87.5 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	4.1 A	Power Factor	76.4
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	K
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Mounting	Rigid Base	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	Special Extension Both Sides
Assembly/Box Mounting	F1 ONLY		
Outline Drawing	OL132174	Connection Drawing	005433.09

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:08/24/2023