



Nameplate Specifications

Phase	3	Output HP	2 & 2 Hp
Output KW	1.5 & 1.5 kW	Voltage	230/460 & 190-208/380-415 V
Speed	1170 & 970 rpm	Service Factor	1.15 & 1.15
Frame	184TV	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Efficiency	86.5 %
Ambient Temperature	65 °C	Frequency	60 & 50 Hz
Current	7.2/3.6 & 8-8.2/4-4.1 A	Power Factor	60
Duty	Continuous	Insulation Class	H
Design Code	B	KVA Code	L
Drive End Bearing Size	6207	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Resistance Main	6.2 Ohms	Mounting	Rigid Base
Motor Orientation	Shaft Up	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Shaft Diameter	1.125 in
Assembly/Box Mounting	W8		
Outline Drawing	OL132194-850	Connection Drawing	005010.01