

PRODUCT INFORMATION PACKET



Model No: 132195.00
Catalog No: 132195.00
5.5HP..1750RPM.184.DP./V.1PH.60HZ..NOT.40C..C FACE..C184K17DC8A

Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E





Nameplate Specifications

Output HP	5.50 Hp	Output KW	4.1 kW
Frequency	60 Hz	Voltage	208-230 V
Current	29.0-30.0 A	Speed	1740 rpm
Service Factor	1	Phase	1
Efficiency	81.9 %	Power Factor	94.3
Duty	15 Minute	Insulation Class	F
Design Code	L	KVA Code	H
Frame	184TC	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		


Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1 ONLY		
Connection Drawing	005018.01	Outline Drawing	OL132195

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/18/2023


005018-01

VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



* THIS LEAD MAY BE WHITE

LINE LEADS

ROTATION
FACING
LEAD END

L1

L2

C.C.W.


T1,T8

T4,T5

C.W.

T1,T5

T4,T8

				TOLERANCES UNLESS SPECIFIED		 Regal Beloit America, Inc.	DRAWN ADH 02/19/74			
				DEC.	INCHES		CHK WRK 02/20/74			
							APPD JCW 02/20/74			
21	LOGO UPDATED FROM LEESON TO MARATHON	AS 07/03/19	AS	.X	±.1					
20	ALTERNATE T5 LEAD MARKING WAS RED	RLW 7/22/02	KH	.XX	±.01	TITLE EXTERNAL WIRING DIAGRAM TYPE "K" W/O PROTECTOR	SCALE 1=1			
19	ADDED ALTERNATE T5 LEAD MARKING	RLW 5/31/02	KH	.XXX	±.005		REF			
18	REDRAWN ON CAD	DBT 06/24/97		.XXXX	±.0005	MAT'L. DECAL - 004018	FMF			
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH	PREV			
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT			RFP		CAD FILE 00501801		SIZE	DRAWING NO.		REV.
			DIST BRF-NLV				A	005018-01		21