

Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	208-230/460 V
Current	26.0-24.0/12.0 A	Speed	3450 rpm
Service Factor	1.15	Phase	3
Efficiency	88.1 %	Power Factor	89.4
Duty	30 Minute	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	J
Frame	182TZ	Enclosure	Open Enclosed
Thermal Protection	Thermostat	Ambient Temperature	50 °C
Drive End Bearing Size	NONE	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	10
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	2	Rotation	Reversible
Resistance Main	1.1 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.343 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Connection Drawing	005010.36	Outline Drawing	OL132226