



Nameplate Specifications

Output HP	2 Hp	Output KW	1.5 kW
Frequency	60 Hz	Voltage	575 V
Current	2.9 A	Speed	1170 rpm
Service Factor	1.15	Phase	3
Efficiency	86.5 %	Power Factor	60
Duty	Continuous	Insulation Class	H
Design Code	B	KVA Code	L
Frame	184TV	Enclosure	Totally Enclosed Air Over
Thermal Protection	No Protection	Ambient Temperature	65 °C
Drive End Bearing Size	6207	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Shaft Up	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1 ONLY		
Outline Drawing	OL132272	Connection Drawing	005102.01