

Nameplate Specifications

Output HP	10 Hp	Output KW	7.5 kW
Frequency	60 Hz	Voltage	208-220 V
Current	47.0-46.0 A	Speed	3450 rpm
Service Factor	1	Phase	1
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	C
Frame	182TZ	Enclosure	Open Enclosed
Thermal Protection	Thermostat	Ambient Temperature	50 °C
Drive End Bearing Size	NONE	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	10
Number of Speeds	1		

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Resistance Main	.3 Ohms	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.343 in
Assembly/Box Mounting	F3		
Connection Drawing	005058.05	Outline Drawing	OL132283

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022