

PRODUCT INFORMATION PACKET



Model No: 132316.00

Catalog No: 132316.00

..2HP..1170RPM.184T.TEFC.208-230/460V.3PH.60HZ.Cont.50C.1.15SF.RIGID.C184T11FB30.....NONE.....

Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2023 Regal Rexnord Corporation, All Rights Reserved. MC017097E






Nameplate Specifications

Output HP	2 Hp	Output KW	1.5 kW
Frequency	60 Hz	Voltage	220/440 V
Current	6.8/3.4 A	Speed	1170 rpm
Service Factor	1.15	Phase	3
Efficiency	88.5 %	Power Factor	65
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	J
Frame	184T	Enclosure	Totally Enclosed Fan Cooled
Thermal Protection	No Protection	Ambient Temperature	50 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Resistance Main	5.4 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1 ONLY		
Connection Drawing	005010.01	Outline Drawing	OL132316

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:01/18/2023






- NOTES:
- 1) GASKETS THROUGHOUT
 - 2) EPOXY PAINT
 - 3) VARNISH ON INTERNAL COMPONENTS.
 - 4) FRAME AND CONDUIT BOX DRAIN HOLES OPEN

		TOLERANCES UNLESS SPECIFIED		LEESON		ELECTRIC MOTORS GEARMOTORS AND DRIVES		DRAWN VS 1/17/2012	
		DEC INCHES						CHK	
		X ±.1						APPR	
		XX ±.03		TITLE		OUTLINE - 180T FRAME		SCALE 1:2	
		XXX ±.005				TEFC - RIGID		REF OLPR112048	
		XXXX ±.0005		MAT'L				FMF	
NO		REVISION		BY & DATE		CHK ANG ±1/2°		PAGE OF	
		THIRD ANGLE PROJECTION		RFP		FINISH		SIZE	
						PREV		DRAWING NO	
						NETWORK FILE NAME OL132316		B	
								OL132316	
								REV	

005010-01

VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



				TOLERANCES UNLESS SPECIFIED		 Regal Beloit America, Inc.			DRAWN RDW 04/12/02		
				DEC.	INCHES				CHK		
				.X	±.1				APPD		
				.XX	±.01				SCALE 1=1		
				.XXX	±.005	TITLE EXTERNAL WIRING DIAGRAM 3 PHASE W/O PROTECTOR			REF FIG.2-51		
A	UPDATED TO REGAL LOGO	SAJ 06/26/15	AJY	.XXXX	±.0005				MAT'L. DECAL - 004014		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH			PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP 04/12/02		CAD FILE 00501001			SIZE A	DRAWING NO. 005010-01	REV A
				DIST BRF-NLV							