



Nameplate Specifications

Phase	3	Output HP	3 Hp
Output KW	2.2 kW	Voltage	208-230/460 V
Speed	1740 rpm	Service Factor	1.15
Frame	182TCV	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	No Protection	Efficiency	82.8 %
Ambient Temperature	40 °C	Frequency	60 Hz
Current	9.2-9.0/4.5 A	Power Factor	75.5
Duty	Continuous	Insulation Class	F
Design Code	C	KVA Code	K
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Reversible
Resistance Main	4.76 Ohms	Mounting	Round
Motor Orientation	Horizontal Or Up Or Down	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Outline Drawing	OL132333	Connection Drawing	005010.15

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024