



Nameplate Specifications

Phase	3	Output HP	10 Hp
Output KW	7.5 kW	Voltage	575 V
Speed	3476 rpm	Service Factor	1.15
Frame	182TZ	Enclosure	Open Enclosed
Thermal Protection	Thermostat	Efficiency	88.1 %
Ambient Temperature	50 °C	Frequency	60 Hz
Current	9.5 A	Power Factor	89.4
Duty	Continuous	Insulation Class	F
Design Code	B	KVA Code	J
Drive End Bearing Size	NONE	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	10
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Wye Start Delta Run
Poles	2	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.343 in
Assembly/Box Mounting	F3		
Outline Drawing	OL132336	Connection Drawing	005190.02

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024