

# PRODUCT INFORMATION PACKET



Model No: 132404.00  
Catalog No: 132404.00  
PR135562..7HP...184TZ.TENV.34V.3PH..INVERTER DUTY.40C.1.0SF.....

Regal and Leeson are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2024 Regal Rexnord Corporation, All Rights Reserved. MC017097E





### Nameplate Specifications



Phase	3	Output HP	SPECIAL Hp
Voltage	- V	Speed	1111 rpm
Frame	184TZ	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	No Protection	Ambient Temperature	40 °C
Frequency	- Hz	Current	- A
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	E
Drive End Bearing Size	NONE	Opp Drive End Bearing Size	NONE
UL	No	CSA	N
CE	N	IP Code	43
Number of Speeds	1		

### Technical Specifications


Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Rotation	Reversible	Mounting	Round
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Assembly/Box Mounting	F1 ONLY
Outline Drawing	OL132404	Connection Drawing	NONE

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:09/07/2024

OL132404



NOTE:  
ALL PARTS TO BE SHIPPED LOOSE  
OUTLINE IS FOR REFERENCE ONLY

				TOLERANCES UNLESS SPECIFIED		 ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN UD 10-10-14			
				DEC.	INCHES		CHK SR 10-10-14			
				.X	±.1		APPD			
				.XX	±.03		TITLE OUTLINE 184T FRAME PARTIAL MOTOR	SCALE 1=4		
				.XXX	±.005			REF OL132185		
				.XXXX	±.0005	MAT'L.	FMF			
NO.	REVISION	BY & DATE	CHK	ANG	±1/2'	FINISH HI PERFORMANCE GOLF CARS INC			PREV	
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT – DO NOT SCALE THIS PRINT			RFP		CAD FILE OL132404			SIZE A	DRAWING NO. OL132404	PAGE OF REV.
			DIST							