



Nameplate Specifications

Output HP	3 Hp	Output KW	2.2 kW
Frequency	60 Hz	Voltage	115/208-230 V
Current	33.5/18.0-16.8 A	Speed	1740 rpm
Service Factor	1	Phase	1
Efficiency	76.2 %	Power Factor	75.6
Duty	15 Minute	Insulation Class	F
Design Code	L	KVA Code	J
Frame	184TC	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Manual	Ambient Temperature	40 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Induction Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Mounting	Round	Motor Orientation	Horizontal
Drive End Bearing	Ball	Opp Drive End Bearing	Ball
Frame Material	Rolled Steel	Shaft Type	T
Assembly/Box Mounting	F1 ONLY		
Connection Drawing	005067.02	Outline Drawing	036142-1100

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:03/30/2023