



Nameplate Specifications

Phase	3	Output HP	2 & 1.50 Hp
Output KW	1.5 & 1.1 kW	Voltage	208-230/460 & 200/400 V
Speed	1170 & 960 rpm	Service Factor	1.15 & 1.15
Frame	182TC	Enclosure	Totally Enclosed Non Ventilated
Thermal Protection	Automatic	Efficiency	80 & 80 %
Ambient Temperature	40 °C	Frequency	60 & 50 Hz
Current	8-7.2/3.6 & 12/6 A	Power Factor	65.7
Duty	60 Minute	Insulation Class	H
Design Code	B	KVA Code	L
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	43
Number of Speeds	1		

Technical Specifications

Electrical Type	Squirrel Cage Induction Run	Starting Method	Across The Line
Poles	6	Rotation	Reversible
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	036240-900	Connection Drawing	005020.02

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:06/23/2023