



Nameplate Specifications

Phase	1	Output HP	5 & 7 Hp
Output KW	3.7 & 5.2 kW	Voltage	230 & 230 V
Speed	3510 & 3470 rpm	Service Factor	1.0 & 1.0
Frame	184TZ	Enclosure	Open Air Over
Thermal Protection	No Protection	Efficiency	81 & 82.5 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	21.3 & 29 A	Power Factor	92.9
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	G
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	10
Number of Speeds	1		

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Resistance Main	.2621 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Overall Length	16.82 in
Frame Length	11.50 in	Shaft Diameter	1.125 in
Shaft Extension	3.94 in	Assembly/Box Mounting	F1/F2 CAPABLE
Outline Drawing	OL132636	Connection Drawing	005368.10