

# PRODUCT INFORMATION PACKET

Model No: 132630.00

Catalog No: 132630.00

132630.00..5HP..1740RPM.184T.DP.208-230V.1PH.60HZ.CONT.40C.1.15SF.RIGID.....

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.  
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



### Nameplate Specifications


Output HP	5 Hp	Output KW	3.7 kW
Frequency	60 Hz	Voltage	208-230 V
Current	23.0-21.0 A	Speed	1740 rpm
Service Factor	1.15	Phase	1
Efficiency	83 %	Power Factor	94
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	H
Frame	184T	Enclosure	Drip Proof
Thermal Protection	No Protection	Ambient Temperature	40 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	N	IP Code	22
Number of Speeds	1		

### Technical Specifications


Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	4	Rotation	Selective Counterclockwise
Resistance Main	.48 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005018.01	Outline Drawing	035370-1050

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/01/2022




DRAWING REVISION E		REVISION BY NK		DATE 8/28/18		TOLERANCES UNLESS OTHERWISE SPECIFIED: DEC. INCH mm ANGLE .X ±0.1 [±2.5] ±0.5° .XX ±0.01 [±0.25] .XXX ±0.005 [±0.127] .XXXX ±0.0005 [±0.0127] REMOVE BURRS & BREAK SHARP EDGES: .003/.015 [0.076/.381] X 45° CORNER FILLETS: R.02 [.51] MACHINED SURFACES: 125 √ 3.2 / INCH mm √ mm SHOWN IN [BRACKETS]		DRAWN BY PG		 <b>Regal</b> Beloit America, Inc.			
ECO ECO-0151575		APPROVED BY SR		DATE 8/28/18				DATE 10/02/97					
ECO DESCRIPTION						REFERENCE		MATERIAL		PROCESS/FINISH			
<b>WHEN REQ'D NOTE ADDED</b> COPYRIGHT REGAL BELOIT AMERICA, INC. ALL RIGHTS RESERVED. PROPRIETARY AND CONFIDENTIAL INFORMATION - THIS DOCUMENT IS THE PROPERTY OF REGAL BELOIT AMERICA, INC. ("OWNER") AND CONTAINS OWNER'S PROPRIETARY INFORMATION. ANY PERSON, CORPORATION OR OTHER FIRM RECEIVING IT IS DEEMED, BY RECEIVING IT, TO AGREE THAT IT, AND/OR ANY PART OF IT, SHALL NOT BE DISCLOSED TO ANY PERSON, CORPORATION OR OTHER ENTITY, DUPLICATED, AND/OR USED, EXCEPT AS EXPRESSLY APPROVED IN WRITING IN ADVANCE BY OWNER. THIS DOCUMENT SHALL BE RETURNED TO OWNER UPON REQUEST. IT MAY BE SUBJECT TO CERTAIN RESTRICTIONS UNDER APPLICABLE EXPORT CONTROL LAWS AND REGULATIONS.						DESCRIPTION <div style="text-align: center;"> <b>OUTLINE</b>          DRIP PROOF - RIGID MOUNT       </div>		SIZE <b>B</b>		DRAWING NUMBER <div style="text-align: center;"> <b>035370</b> </div>		SHEET 1 OF 1	

VIEW FROM OUTSIDE OF MOTOR AT SWITCH END.



\* THIS LEAD MAY BE WHITE

## LINE LEADS

ROTATION  
FACING  
LEAD END

L1

L2

C.C.W.

T1,T8

T4,T5

C.W.

T1,T5

T4,T8

NO.	REVISION	BY & DATE	CHK	ANG	TOLERANCES UNLESS SPECIFIED		TITLE	DRAWN ADH 02/19/74
					DEC.	INCHES		
21	LOGO UPDATED FROM LEESON TO MARATHON	AS 07/03/19	AS	.X	±.1		EXTERNAL WIRING DIAGRAM TYPE "K" W/O PROTECTOR	CHK WRK 02/20/74
20	ALTERNATE T5 LEAD MARKING WAS RED	RLW 7/22/02	KH	.XX	±.01			APPD JCW 02/20/74
19	ADDED ALTERNATE T5 LEAD MARKING	RLW 5/31/02	KH	.XXX	±.005			SCALE 1=1
18	REDRAWN ON CAD	DBT 06/24/97		.XXXX	±.0005			REF
							MAT'L. DECAL - 004018	FMF
							FINISH	PREV
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP	CAD FILE 00501801		SIZE A	DRAWING NO. 005018-01
				DIST BRF-NLV				REV. 21



Regal Beloit America, Inc.