



Nameplate Specifications

Phase	1	Output HP	7.50 & 10 Hp
Output KW	5.6 & 7.5 kW	Voltage	230 & 230 V
Speed	3490 & 3440 rpm	Service Factor	1.0 & 1.0
Frame	184TZ	Enclosure	Open Air Over
Thermal Protection	Thermostat	Efficiency	82.5 & 83.2 %
Ambient Temperature	40 °C	Frequency	60 & 60 Hz
Current	31 & 40 A	Power Factor	96.8
Duty	Continuous	Insulation Class	F
Design Code	NO DESIGN CODE	KVA Code	C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	10
Number of Speeds	1		

Technical Specifications

Electrical Type	Permanent Split Capacitor	Starting Method	Across The Line
Poles	2	Rotation	Selective Counterclockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	Single Special Extension	Shaft Diameter	1.125 in
Assembly/Box Mounting	F1/F2 CAPABLE		
Outline Drawing	OL132637	Connection Drawing	00536810