

PRODUCT INFORMATION PACKET

Model No: 132664.00

Catalog No: 132664.00

Fan and Blower Motor, 8 HP, 1 Ph, 60 Hz, 208-230 V, 3600 RPM, 184T Frame, DP

Regal and are trademarks of Regal Rexnord Corporation or one of its affiliated companies.
©2022 Regal Rexnord Corporation, All Rights Reserved. MC017097E



Nameplate Specifications


Output HP	8 Hp	Output KW	6.0 kW
Frequency	60 Hz	Voltage	208-230 V
Current	35.0-32.0 A	Speed	3520 rpm
Service Factor	1.15	Phase	1
Efficiency	84 %	Power Factor	96
Duty	Continuous	Insulation Class	F
Design Code	L	KVA Code	H
Frame	184T	Enclosure	Drip Proof
Thermal Protection	Manual	Ambient Temperature	40 °C
Drive End Bearing Size	6206	Opp Drive End Bearing Size	6205
UL	Recognized	CSA	Y
CE	Y	IP Code	12
Number of Speeds	1		

Technical Specifications

Electrical Type	Capacitor Start Capacitor Run	Starting Method	Across The Line
Poles	2	Rotation	Fixed Clockwise
Resistance Main	0 Ohms	Mounting	Rigid Base
Motor Orientation	Horizontal	Drive End Bearing	Ball
Opp Drive End Bearing	Ball	Frame Material	Rolled Steel
Shaft Type	T	Assembly/Box Mounting	F1 ONLY
Connection Drawing	005056.61	Outline Drawing	035562-1250

This is an uncontrolled document once printed or downloaded and is subject to change without notice. Date Created:11/10/2022


VIEW FROM OUTSIDE OF MOTOR AT SWITCH END



CWLE ROTATION SHOWN

ORACLE REV.
00

LINE LEADS



ROTATION FACING LEAD END	L1	L2 (BLANK)	JOIN
C.C.W.	P1	T4, T5	P2, T8
C.W.	P1	T4, T8	P2, T5

				TOLERANCES UNLESS SPECIFIED		ELECTRIC MOTORS GEARMOTORS AND DRIVES	DRAWN	LST 9/6/16	
				DEC.	INCHES		CHK		
				.X	±.1		APPD		
				.XX	±.01		SCALE	1=1	
				.XXX	±.005	TITLE	EXTERNAL WIRING DIAGRAM TYPE "K" W/PROTECTOR		
A	RELEASED	LST	9/6/16	.XXXX	±.0005	MAT'L.	REF		
NO.	REVISION	BY & DATE	CHK	ANG	±1/2"	FINISH	PREV		
THIS DRAWING IN DESIGN AND DETAIL IS OUR PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH OUR WORK ALL RIGHTS OF DESIGN AND INVENTION ARE RESERVED THIS IS AN ELECTRONICALLY GENERATED DOCUMENT - DO NOT SCALE THIS PRINT				RFP	CAD FILE	00505661ME	SIZE	DRAWING NO.	REV.
				DIST	NLV		A	005056-61	A